



144" 36K Guy Strain, Clevis / Clevis + 2 Rollers

by CHANCE Utility
Catalog ID: GS36144CC2

144" Fiberglass Guy Strain- 36,000 lb Series- Clevis / Clevis + 2 Rollers



* Representative image

Product Details

General

Description - End Fitting	Clevis - Clevis - 2 Rollers
Strength Rating - Ultimate	36000 lb
Tensile Strength	36000 lb
UPC	096359441342

Dimensions

Diameter - Rod / Tube	0.875 in
Length	144.00 in
Length - Clevis Pin Center to Clevis Bottom	2.12 in
Mounting Bolt Spacing	159.00 in
Weight	13.8 lb

Logistics

Carton Quantity	4 EA
Pallet Quantity	100 EA
Standard Package	4

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com