

EFV Model P33 with SERIES 1100

By Gas Breaker
Catalog # [20264GB](#)

EFV #P33 3/4" IPS, 2406 W/ 3/4"IPS SOCKET CPLG. IN/OUT,
SERIES 1100



Features

- Work with the flow of natural gas as the sensing source
- Activate when a line rupture causes an excess flow condition
- Automatically reset and resume normal operation after repairs are made using a slight gas bypass to re-pressurize the line. Install in minutes with standard tools
- Operate within your normal service line sizing requirements to avoid tripping by snap-acting loads
- Higher capacity EFVs can accommodate future increases in gas loads.
- Maintain stability under turbulent flow conditions by using a unique, dynamically balanced float
- Available for virtually all pressures and service line capabilities
- In-line installation makes them tamper-proof
- Can be fabricated with fitting and piping materials from most manufacturers

General

Application	3/4" IPS, 2406, W/3/4" IPS SOCKET In/Out
Material	PE Polyethylene (2406/2708)

Product Assets

[Catalogs - Gas Breaker - Automatic Safety Valves for Gas Service Lines](#)