



EFV Model P41 with SERIES 800

By Gas Breaker
Catalog # [25079GB](#)

EFV #P41 1/2" CTS .090 3408, 12" LONG, SERIES 800



Features

- Work with the flow of natural gas as the sensing source
- Activate when a line rupture causes an excess flow condition
- Automatically reset and resume normal operation after repairs are made using a slight gas bypass to re-pressurize the line. Install in minutes with standard tools
- Operate within your normal service line sizing requirements to avoid tripping by snap-acting loads
- Higher capacity EFVs can accommodate future increases in gas loads.
- Maintain stability under turbulent flow conditions by using a unique, dynamically balanced float
- Available for virtually all pressures and service line capabilities
- In-line installation makes them tamper-proof
- Can be fabricated with fitting and piping materials from most manufacturers

Application

1/2" CTS .090 3408, 12" LONG

General

Catalog Number	25079GB
Material	PE Polyethylene (3408/4710)

Dimensions

Length	12 in
--------	-------

Product Assets

[Catalogs - Gas Breaker - Automatic Safety Valves for Gas Service Lines](#)
[Specifications - 25079GB](#)