

Titan (analogue), yellow, steel cord, O button (autodial) - CE Marked

By GAI-Tronics

Catalog # [028-02-2830-652](#)

Titan's aluminium body is robust and designed to last longer in hostile outdoor environments. Along with weather and vandal resistance, the Titan range meets the acoustic performance, reliability and varying applications demanded by today's markets. The standard analogue unit provides basic telephone functions and can be connected to any standard two-wire telephone line, including FXS ports, analogue PABX lines and PSTN.



General

| | |
|---------------------------|-------------------------------|
| CE Compliant | Yes |
| Catalog Number | 028-02-2830-652 |
| Color | Yellow |
| Connectivity Options | Analogue |
| Mount location | Surface-Mount & Post-Mounting |
| Operating Temperature | -20° C to +60° C |
| Storage Temperature Range | -40° C to +70° C |
| Type | O Button |

Certifications And Compliance

| | |
|--------------|-----|
| CE Compliant | Yes |
|--------------|-----|

Product Assets

[Certifications - Titan and Commander full dialling and auto-dialling analogue telephones Declaration of Conformity](#)

[Installation Manuals - Installation and User Guide for Titan Telephone \(1066\) Commander Telephone \(1065\) Standard keypad models](#)

[Literature - Titan - Metal Bodied Weather Resistant Telephone \(Analogue, Smart Analogue, VoIP\)](#)