

Audio Messenger Interface - Rackmount

By GAI-Tronics
Catalog # 10959-207



The innovative Audio Messenger Interface (AMI) from GAI-TRONICS® provides superior quality digital tone/speech generation and offers telephone interface and feedback elimination capability. A Compact Flash™ Card Kit stores the configuration programming, the voice and tone recordings, and provides CD-quality sound reproduction. With the capability to generate emergency tone alarms, pre-recorded voice messages, and automated normal operation announcements, the AMI is the answer to many communications needs.

Features

- Customer Configurable
- Alarm Tones and Messages ([Tone Reference Library](#))
- User Recordable Messages
- Built-in feedback eliminator
- CD Quality playback
- Real-time clock
- Compact Flash™ Card Kit for Alarm and Message Storage
- Telephone Interface to PA
- [Audio Messenger Interface \(AMI\) ACT Software Download](#)

General

Color	Black
Mount location	Rackmount
Operating Temperature Range Celcius	0° C to +50° C @ 20-80% humidity, non-condensing
Power Consumption	12-26 VDC, Class II power supply optional
Type	Digital Speech Player Alarm Generator Telephone Interface

Dimensions

Cubic Capacity	326.9032 cu.in
Depth	11.18
Height	1.72 in
Width	17 in

Electrical Ratings

Frequency Rating	20-20000 Hz
------------------	-------------

Certifications And Compliance

Certified Listed	NRTL Listed to UL 60950
	CAN/CSA-C22.2 No. 60950-00
	IEC 60950

Product Assets

- [Installation Manuals - Rack-Mount Audio Messenger Interface](#)
- [Installation Manuals - AMI Redundant Controller Modules - Model 10962-001 and 10962-002](#)
- [Installation Manuals - Model 12584-001 I/O Control Module](#)
- [Literature - Audio Messenger Interface](#)
- [Literature - AMI Input Form](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
GTC-10959207-SPEC-EN | REV 6/2024