

Audio Messenger Interface - Rackmount

By GAI-Tronics
Catalog # 10959-208



The innovative Audio Messenger Interface (AMI) from GAI-TRONICS® provides superior quality digital tone/speech generation and offers telephone interface and feedback elimination capability. A Compact Flash™ Card Kit stores the configuration programming, the voice and tone recordings, and provides CD-quality sound reproduction. With the capability to generate emergency tone alarms, pre-recorded voice messages, and automated normal operation announcements, the AMI is the answer to many communications needs.

Features

- Customer Configurable
- Alarm Tones and Messages ([Tone Reference Library](#))
- User Recordable Messages
- Built-in feedback eliminator
- CD Quality playback
- Real-time clock
- Compact Flash™ Card Kit for Alarm and Message Storage
- Telephone Interface to PA
- [Audio Messenger Interface \(AMI\) ACT Software Download](#)

General

Catalog Number	10959-208
Color	Black
Mount location	Rackmount
Operating Temperature Range Celcius	0° C to +50° C @ 20-80% humidity, non-condensing
Power Consumption	12-26 VDC, Class II power supply optional
Type	<ul style="list-style-type: none"> • Digital Speech Player • Alarm Generator • Telephone Interface

Dimensions

Cubic Capacity	326.9032 cu.in
Depth	11.18
Height	1.72 in
Width	17 in

Electrical Ratings

Frequency Rating	20-20000 Hz
------------------	-------------

Certifications And Compliance

Certified Listed	<ul style="list-style-type: none"> • NRTL Listed to UL 60950 • CAN/CSA-C22.2 No. 60950-00 • IEC 60950
------------------	--

Product Assets

- [Installation Manuals - Model 12584-001 I/O Control Module](#)
- [Installation Manuals - Rack-Mount Audio Messenger Interface](#)
- [Installation Manuals - 10960 Series Zone Interface Modules](#)
- [Installation Manuals - AMI Redundant Controller Modules - Model 10962-001 and 10962-002](#)
- [Literature - Audio Messenger Interface](#)
- [Literature - AMI Input Form](#)
- [Specifications - 10959-208](#)