

Titan (VoIP), steel cord, 0 button (CE Marked)

By GAI-Tronics
Catalog # 114-02-0010-121

Titan's aluminium body is robust and designed to last longer in hostile outdoor environments. Along with weather and vandal resistance, the Titan range meets the acoustic performance, reliability and varying applications demanded by today's markets. GAI-TRONICS VoIP-SIP telephones support Power over Ethernet (PoE) to combine power and connection to LAN or WAN, offering a wealth of additional features including real-time reporting via SNMP and can be configured by web browser. *

Contact GAI-TRONICS for clarification of application



General

CE Compliant	Yes
Color	Gray
Connectivity Options	VoIP
Mount location	Surface-Mount & Post-Mounting
Operating Temperature	-40° C to +60° C
Storage Temperature Range	-40° C to +70° C
Type	0 Button

Certifications And Compliance

CE Compliant	Yes
--------------	-----

Product Assets

[Certifications - EU Declaration of Conformity \[Titan VoIP Telephones\]](#)

[Configuration Guide - VoIP Telephone Configuration Guide: Firmware versions 1193 Telephones \(v1.08\); 1201 Telephones for Auteldac 6 \(v1.08\)](#)

[Installation Manuals - Installation and User Guide for Rugged VoIP Telephone Titan, Commander and Help Point \(1193 models\)](#)

[Literature - Titan - Metal Bodied Weather Resistant Telephone \(Analogue, Smart Analogue, VoIP\)](#)

[Video - Titan VoIP Installation](#)