

Titan VoIP Illuminated Crossing Phone

By GAI-Tronics

Catalog # 114-02-0111-152

The Titan Illuminated Crossing telephone is specifically designed for installation at automatic half barrier (AHB) level crossings.

Features

- Designed for AHB Level Crossings
- SIP Compatible (RFC3261)
- Large Illuminated Panel
- Raised Stainless Steel Button
- Soft Sprung Door with Magnetic Catch
- Industry standard robust handset c/w armoured cord
- Selectable Call Timer
- Diversion (Memory List)
- Power over Ethernet Compatible
- Real-Time Alarm Reporting via SNMP
- Robust and Weather Resistant Up to IP66
- CE compliant

Application

AHB Level Crossings

General

CE Compliant Yes



Catalog Number	114-02-0111-152
Color	Yellow
Connectivity Options	VoIP
Operating Temperature	-40° C to +60° C
Storage Temperature Range	-40° C to +70° C
Type	1 Button
Weather Rating	Up to IP66
Weather Resistant	Yes

Certifications And Compliance

CE Compliant Yes

Product Assets

Configuration Guide - VoIP Telephone Configuration Guide:

Firmware versions 1193 Telephones (v1.08); 1201 Telephones for Auteldac 6 (v1.08)

Installation Manuals - VoIP Titan Illuminated Crossing Telephone
(1193 model) Installation & User Guide

Literature - Titan VoIP Illuminated Crossing Phone

Specifications - 11402011152