

Commander (VoIP) yellow, steel cord, 0 button (CB) - CE Marked

By GAI-Tronics
Catalog # [115-02-0010-112](#)

The **Commander** family of telephones are tough, weather resistant units built to withstand abuse and environmental extremes; moulded in glass filled polyester to prevent rust and corrosion. It is simple to install with fixings concealed from view giving increased security from vandalism. GAI-TRONICS' VoIP-SIP telephones support Power over Ethernet (PoE) to combine power and connection to LAN or WAN, offering a wealth of additional features including real-time reporting via SNMP, and can be configured by web browser.



General

CE Compliant	Yes
Color	Yellow
Connectivity Options	VoIP
Mount location	Surface-Mount & Post-Mounting
Operating Temperature	-40° C to +60° C
Output Level Ringer	80 dBA @ 2 ft.
Signal Type	VoIP - SIP
Type	<ul style="list-style-type: none"> • 0 Button • Weather Resistant & Vandal Resistant Telephones
Weather Rating	IP65

Dimensions

Dimensions	5.5 in x 7.5 in x 11.5 in
Height	11.5 in
Length	5.5 in
Weight	7 lb
Width	7.5 in

Electrical Ratings

Signal	Ethernet
Voltage Rating Description	24-48 VDC or PoE

Certifications and Compliance

CE Compliant	Yes
--------------	-----

Product Assets

[Catalogs - Offshore Wind Industry - Products for Wind Applications](#)
[Certifications - EU Declaration of Conformity \[Commander VoIP Telephones\]](#)
[Configuration Guide - VoIP Telephone Configuration Guide: Firmware versions 1193 Telephones \(v1.08\); 1201 Telephones for Auteldac 6 \(v1.08\)](#)
[Installation Manuals - Installation and User Guide for Rugged VoIP Telephone Titan, Commander and Help Point \(1193 models\)](#)
[Literature - Commander Telephone](#)