



VR Help Point (VoIP), 1 button (faceplate only)

By GAI-Tronics
Catalog # [116-02-0011-001](#)

The VR Help Point family of telephones is fully electronic, vandal and weather resistant. It provides hands-free loudspeaking communications for any public area. GAI-TRONICS' VoIP-SIP telephones support Power over Ethernet (PoE) to combine power and connection to LAN or WAN, offering a wealth of additional features including real-time reporting via SNMP, and can be configured by web browser.



General

CE Compliant	Yes
Color	Gray
Connectivity Options	VoIP
Mount location	Flush-Mount
Operating Temperature	-40° C to +60° C
Power Supply	External 24-48 VDC or Power-Over-Ethernet (PoE 802.3af compliant); power requirement 7W max (4W idle)
Signal Type	VoIP - SIP
Type	One-Button
Weather Rating	IP65

Dimensions

Dimensions	1.9 in x 7.1 in x 13.9 in
Height	13.9 in
Length	1.9 in
Weight	4.4 lb
Width	7.1 in

Electrical Ratings

Signal	Ethernet
--------	----------

Certifications and Compliance

CE Compliant	Yes
--------------	-----

Product Assets

[Certifications - EU Declaration of Conformity \[Help Point VoIP Telephones\]](#)
[Configuration Guide - VoIP Telephone Configuration Guide: Firmware versions 1193 Telephones \(v1.08\); 1201 Telephones for Auteldac 6 \(v1.08\)](#)
[Installation Manuals - Installation and User Guide for Rugged VoIP Telephone Titan, Commander and Help Point \(1193 models\)](#)
[Literature - VR Help Point \(Vandal Resistant\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
GTC-116-02-0011-001-SPEC-EN | REV 7/2023