

DDA Help Point (VoIP) 1 button, hands-free (faceplate only)

By GAI-Tronics
Catalog # [116-02-0021-102](#)

This Help Point incorporates features to assist with special needs and designed to comply with The Equality Act 2010 (EA). It is finished in contrasting colours, with a raised 32mm button. Raised text, Braille and inductive loop are standard. The Help Point telephones are vandal and weather resistant, providing hands-free loudspeaking communications for any public area. The internal components are protected by a weather resistant enclosure behind the faceplate. The VoIP-SIP telephone supports Power over Ethernet (PoE) to combine power and connection to LAN or WAN, offering a wealth of additional features including real-time reporting via SNMP, and can be configured by web browser.



General

CE Compliant	Yes
Color	Yellow
Connectivity Options	VoIP
Mount location	Flush-Mount
Operating Temperature	-40° C to +60° C
Signal Type	VoIP - SIP
Storage Temperature Range	-40° C to +70° C
Type	One-Button
Weather Rating	IP65

Dimensions

Dimensions	1.9 in x 7.1 in x 13.9 in
Height	13.9 in
Length	1.9 in
Weight	8.8 lb
Width	7.1 in

Electrical Ratings

Signal	Ethernet
Voltage Rating Description	24-48 VDC or PoE

Certifications and Compliance

CE Compliant	Yes
--------------	-----

Product Assets

[Catalogs - Transportation - Rail Industry](#)
[Certifications - EU Declaration of Conformity \[Help Point VoIP Telephones\]](#)
[Configuration Guide - VoIP Telephone Configuration Guide: Firmware versions 1193 Telephones \(v1.08\); 1201 Telephones for Auteldac 6 \(v1.08\)](#)
[Installation Manuals - Installation and User Guide for Rugged VoIP Telephone Titan, Commander and Help Point \(1193 models\)](#)
[Literature - DDA Help Point](#)