

VR Help Point (VoIP), 1 button (faceplate only)

By GAI-Tronics
 Catalog # [116-02-0011-001](#)

The VR Help Point family of telephones is fully electronic, vandal and weather resistant. It provides hands-free loudspeaking communications for any public area. GAI-TRONICS' VoIP-SIP telephones support Power over Ethernet (PoE) to combine power and connection to LAN or WAN, offering a wealth of additional features including real-time reporting via SNMP, and can be configured by web browser.

Features

- VR Help Point VoIP
- SIP compatible
- 0 Button Memory dial
- CE Marked
- Faceplate only

General

CE Compliant	Yes
Catalog Number	116-02-0011-001
Color	Gray
Connectivity Options	VoIP
Mount location	Flush-Mount
Operating Temperature	-40° C to +60° C
Power Supply	External 24-48 VDC or Power-Over-Ethernet (PoE 802.3af compliant); power requirement 7W max (4W idle)
Signal Type	VoIP - SIP
Specifications	CE
Type	One-Button
Weather Rating	IP65

Dimensions



Dimensions	1.9 in x 7.1 in x 13.9 in
Dimensions - Shipping	14.5 x 9.0 x 5.75
Height	13.9 in
Length	1.9 in
Weight	4.4 lb
Width	7.1 in

Electrical Ratings

Signal	Ethernet
--------	----------

Certifications And Compliance

CE Compliant	Yes
--------------	-----

Product Assets

[Certifications - EU Declaration of Conformity \[Help Point VoIP Telephones\]](#)
[Configuration Guide - VoIP Telephone Configuration Guide: Firmware versions 1193 Telephones \(v1.08\); 1201 Telephones for Auteldac 6 \(v1.08\)](#)
[Installation Manuals - Installation and User Guide for Rugged VoIP Telephone Titan, Commander and Help Point \(1193 models\)](#)
[Literature - VR Help Point \(Vandal Resistant\)](#)
[Specifications - 116020011001](#)