

Aluminum Horns - Model 13302-002

By GAI-Tronics
Catalog # [13302-002](#)

GAI-TRONICS provides loudspeakers designed for the reproduction and broadcast of voice communications and pre-recorded tones and speech messages. These loudspeakers are typically used in industrial and commercial locations such as manufacturing plants, metal and chemical processing facilities, and warehouses.

Features

- Aluminum horns with gray epoxy finish for corrosion and weather resistance
- Excellent performance in voice frequencies
- Steel mounting bracket for easy vertical or horizontal positioning
- Separate driver allows flexibility in applications
- 1 3/8 in. UNEF thread (female) provided for driver connection
- Available with all stainless hardware and Type 316 stainless steel bracket; add "SB" to model number
- 65 Degree Nominal Dispersion Angle
- 20.5" Diameter Horn

General

- Compatibility
- Use Mounting Assembly 411A For Driver 13314 Series
 - Use Mounting Assembly 415A For Driver 13310 Series



Dimensions

Diameter	20.5 in
Length	20.4 in

Product Assets

[Brochures - Loudspeaker Selection Guide](#)
[Installation Manuals - Model 415A and 415A-EP Speaker Mounting Bracket Assemblies](#)
[Installation Manuals - Speaker Mounting Bracket Assemblies \(Models 411A and 411A-EP\)](#)
[Installation Manuals - Speaker/Horn Installation for GAI-TRONICS Communication Systems](#)
[Literature - Industrial Horns and Speakers](#)

Related Products

[13310-201 - Explosionproof Compression Driver - 13310 Series \(16 ohm\)](#)
[13314-001 - Indoor/Outdoor Compression Driver - 13314 Series \(8 ohm\)](#)