

## Bi-Directional Horn - Model 13305-101

By GAI-Tronics  
Catalog # [13305-101](#)

Bi-directional design, effective in hallways or corridors, requires separate driver. Optional epoxy coating offers extra protection against corrosion. 1 3/8" UNEF thread (female) provided for driver connection.



### Features

- Bi-Directional Design Requires One Driver
- Each Horn Provides a Dispersion Angle of 80 Degrees
- Especially Effective in Hallways & Corridors
- Spun Aluminum w/Gray Epoxy Finish
- Mounting Bracket Included
- Accepts GAI-Tronics DIV 1 & DIV 2 Drivers
- Includes 1 3/8" - 18 UNEF Thread (Female) for Driver Connection

### General

Compatibility                      Use Mounting Assembly 413A  
   For Drivers 13310 & 13314  
   Series

### Dimensions

Diameter	8.5 in
Length	20.5 in

### Product Assets

[Brochures - Loudspeaker Selection Guide](#)  
[Installation Manuals - Speaker/Horn Installation for GAI-TRONICS Communication Systems](#)  
[Literature - Industrial Horns and Speakers](#)

### Related Products

[13310-201 - Explosionproof Compression Driver - 13310 Series \(16 ohm\)](#)  
[13314-001 - Indoor/Outdoor Compression Driver - 13314 Series \(8 ohm\)](#)