

Bi-Directional Horn - Model 13305-101

By GAI-Tronics
Catalog # 13305-101



Bi-directional design, effective in hallways or corridors, requires separate driver. Optional epoxy coating offers extra protection against corrosion. 1 3/8" UNEF thread (female) provided for driver connection.

Features

- Bi-Directional Design Requires One Driver
- Each Horn Provides a Dispersion Angle of 80 Degrees
- Especially Effective in Hallways & Corridors
- Spun Aluminum w/Gray Epoxy Finish
- Mounting Bracket Included
- Accepts GAI-Tronics DIV 1 & DIV 2 Drivers
- Includes 1 3/8" - 18 UNEF Thread (Female) for Driver Connection

General

Compatibility Use Mounting Assembly 413A
For Drivers 13310 & 13314 Series

Dimensions

Diameter 8.5 in
Length 20.5 in

Product Assets

[Brochures - Loudspeaker Selection Guide](#)
[Installation Manuals - Speaker/Horn Installation for GAI-TRONICS Communication Systems](#)
[Literature - Industrial Horns and Speakers](#)