

Class I Division 1, 25W Horn Speaker for Gaseous Environments (16 ohm)

By GAI-Tronics
Catalog # [13310-311](#)

The 13310 integral reentrant horn loudspeakers are UL and cUL approved for Class I Division 1 rated areas. Chromated, powder coated and copper free LM6 marine grade enclosures coupled with high impact ABS, UL94 V0 FR horn flares give the speaker a type 4X rating ideal for arduous outdoor environments. All model offerings are fitted with a 316 stainless steel mounting bracket as standard.

Features

- Integral speaker voice coil
- 25W rating

General

Catalog Number	13310-311
Color	Gray
Operating Temperature	-40 °F to +158 °F
Storage Temperature Range	-58°F to +158°F
Weather Rating	NEMA 4, 4X, 3R, 13

Certifications And Compliance



Certification

Certified Listed
Hazardous Rating(s)

- UL
 - cUL
- UL1480 Ed. 6
- Class I Division 1, ABCD, T6, Ta -40°C to +70°C
 - Class I Zone 1, IIC, T6
 - Class I Division 2, ABCD, T6, Ta -40°C to +70°C

Product Assets

[Literature - 25 Watt UL Class I Division 1 Speakers 13310-3xx for Gaseous Environment](#)
[Specifications - 13310311](#)