

Indoor / Outdoor Compression Driver - 13314 Series (70V)

By GAI-Tronics
Catalog # 13314-003

A compression drivers that is designed to provide optimum performance in both commercial and industrial applications. These indoor/outdoor compression drivers are commonly used in light and heavy manufacturing facilities with high ambient noise, and corrosive and hazardous environments.



Features

- Low Distortion, Superior Sound
- Rain-Tight, Chemical Resistant Housing
- Suitable for Harsh or Corrosive Environments
- Variable Impedance Drivers
- Fits GAI-TRONICS' Horns with 1 3/8" - 18 UNEF Threads
- NEMA 4X

General

Operating Temperature	-40° C to +70° C (-40° F to +158° F)
UPC	850025795197

Dimensions

Weight	3.4 lb
--------	--------

Electrical Ratings

Impedance	70V
-----------	-----

Certifications And Compliance

Hazardous Rating(s)	Class I, Div. 2, Groups A, B, C, D
	Class II, Div. 2, Groups F, G
	Class III, Div. 2
Nema Rating	4X

Product Assets

[Installation Manuals - Speaker/Horn Installation for GAI-TRONICS Communication Systems](#)
[Installation Manuals - Model 13314-003 Div. 2 Hazardous Area 70-Volt Horn Driver](#)
[Literature - Indoor / Outdoor Compression Driver](#)



A Hubbell brand