

## UL Div 2, 15 Watt Speakers - 8 ohm

By GAI-Tronics  
Catalog # [13380-001](#)

The 13380-001 to 13380-004 Series Loudspeakers are heavy duty, high output loudspeakers ideal for broadcasting speech announcements and electronic alarm tones in hazardous environments with high ambient noise levels. UL Class I, Division 2 and ABS Type Approved



### General

Material	UL94V0 PPS & ABS with 316 stainless steel bracket
Operating Temperature	-20 °C to + 55 °C
Weather Rating	NEMA Type 4, 4X, 13

### Dimensions

Diameter	7.13 in
Length	10.75 in
Weight	5.5 lb

### Electrical Ratings

Wattage	15 W
---------	------

### Certifications and Compliance

Certification	ABS Type Approval
Certified Listed	<ul style="list-style-type: none"><li>UL File: E165792</li><li>UL File: 1480 &amp; 1480A</li></ul>
Hazardous Rating(s)	<ul style="list-style-type: none"><li>Class I, Div 2, ABCD T4 (135° C) at +55° C</li><li>Class I, Div 2, ABCD T4A (120° C) at +40° C</li><li>Class II, Div 2, FG T6 (85° C) at +55° C</li><li>Class III, Div 1 &amp; 2, T6 (85° C) at +55° C</li></ul>

### Product Assets

[Literature - UL Division 2, 15 Watt Speakers \[13380-001 to 13380-004 Series\]](#)

### Related Products

[Indoor/Outdoor Compression Driver - 13314 Series \(8 ohm\)](#)  
[13314-001 - Indoor/Outdoor Compression Driver - 13314 Series \(8 ohm\)](#)