

UL Div 2, 15 Watt Speakers - 8 ohm

By GAI-Tronics
Catalog # 13380-001

The 13380-001 to 13380-004 Series Loudspeakers are heavy duty, high output loudspeakers ideal for broadcasting speech announcements and electronic alarm tones in hazardous environments with high ambient noise levels. UL Class I, Division 2 and ABS Type Approved



General

Material	UL94V0 PPS & ABS with 316 stainless steel bracket
Operating Temperature	-20 °C to + 55 °C
Weather Rating	NEMA Type 4, 4X, 13

Dimensions

Diameter	7.13 in
Length	10.75 in
Weight	5.5 lb

Electrical Ratings

Wattage	15 W
---------	------

Certifications And Compliance

Certification	ABS Type Approval
Certified Listed	UL File: E165792 UL File: 1480 & 1480A
Hazardous Rating(s)	Class I, Div 2, ABCD T4 (135°C) at +55°C Class I, Div 2, ABCD T4A (120°C) at +40°C Class II, Div 2, FG T6 (85°C) at +55°C Class III, Div 1 & 2, T6 (85°C) at +55°C

Product Assets

[Literature - UL Division 2, 15 Watt Speakers \[13380-001 to 13380-004 Series\]](#)