

UL Div 2, 25 Watt Speakers - 8 ohm

By GAI-Tronics
Catalog # [13381-005](#)

The 13381-005 to 13381-008 Series Loudspeakers are heavy duty, high output loudspeakers ideal for broadcasting speech announcements and electronic alarm tones in hazardous environments with high ambient noise levels.

Features

PAGA Loudspeaker

General

Catalog Number	13381-005
Material	UL94VO PPS & ABS with 316 stainless steel bracket
Operating Temperature	-20 °C to + 55 °C
Weather Rating	NEMA Type 4, 4X, 13

Dimensions

Diameter	8.6 in
Length	12.6 in
Weight	6 lb

Electrical Ratings

Wattage	25 W
---------	------

Certifications And Compliance



Certified Listed

Hazardous Rating(s)

- UL File: E165792
- UL File: 1480 & 1480A
- Class I, Div 2, ABCD T2C (230°C) at +55°C
- Class I, Div 2, ABCD T2D (215°C) at +40°C
- Class II, Div 2, FG T5 (100°C) at +55°C
- Class II, Div 2, FG T6 (85°C) at +40°C
- Class III, Div 1 & 2, T5 (100°C) at +55°C
- Class III, Div 1 & 2, T6 (85°C) at +40°C

Product Assets

[Literature - UL Division 2, 25 Watt Speakers \[13381-005 to 13381-008 Series\]](#)
[Specifications - 13381005](#)