

Corridor Telephone, Keypad (Model 210-001)

By GAI-Tronics
Catalog # [210-001](#)

The corridor telephone offers standard line-powered telephone operation in a rugged, stainless steel package. Its volume-control handset includes a 29-inch, swivel armored cord and the microphone and earpiece are non-accessible. The 210-001 projects less than 4-inches from the mounting surface making it ADA-compliant for corridor installation.

Features

- Surface-Mount design for Indoor Use
- Standard Telephone Operation
- Braille Chrome-plated Keypad
- Brushed Stainless Steel Housing
- Front Panel Pushbutton Volume Control
- Handset with Noise-cancelling Microphone, Hearing Aid-compatible Receiver, and 12-inch Armored Cord with Anchored Lanyard

Application

Corridor Installations

General

Catalog Number	210-001
Color	Silver
Connectivity Options	Analog
Mount location	Surface-Mount
Operating Temperature	-40° F to +140° F (-40° C to +60° C)
Output Level Ringer	90 dBA @ 2 ft.
Signal Type	Analog
Specifications	UL/IC/FCC
Type	Keypad



Weather Rating

Indoor

Dimensions

Dimensions	3.27 in x 5.5 in x 10.0 in
Dimensions - Shipping	13.0 x 12.0 x 8.0
Height	10 in
Length	3.27 in
Weight	5.5 lb
Width	5.5 in

Electrical Ratings

Input Voltage	Phone Line
Signal	Phone Line

Certifications And Compliance

Certified Listed	UL/IC/FCC
------------------	-----------

Product Assets

[Brochures - Rugged Telephone Brochure](#)
[Installation Manuals - Analog Corridor Telephones - Model 210 Series](#)
[Literature - Corridor Telephone Specifications - 210001](#)