



Auteldac 5 (Analogue), curly cord, 0 button; CB, ATEX, noise cancelling with headset socket

By GAI-Tronics
Catalog # [212-02-5020-410](#)

The Auteldac 5 (A5) telephone is an ATEX and IECEx approved, weather resistant unit, designed to withstand arduous industrial atmospheres and environmental extremes.



Application

Hazardous Areas

General

CE Compliant	Yes
Color	Black
Connectivity Options	Analogue
Mount location	Surface-Mount
Operating Temperature	-20° C up to +60° C
Output Level Ringer	90 dBA @ 2 ft.
Signal Type	Analogue
Type	<ul style="list-style-type: none">• 0 Button• CB (Central Battery)
Weather Resistant	Yes

Dimensions

Dimensions	5.5 in x 7.5 in x 11.5 in
Height	11.5 in
Length	5.5 in
Weight	7 lb
Width	7.5 in

Electrical Ratings

Signal	Phone Line
--------	------------

Certifications and Compliance

CE Compliant	Yes
Certification	ATEX

Product Assets

[Installation Manuals - Guide d'installation et d'utilisation for Auteldac 5 Téléphone pour zone à risques certifiée zone 1 Ex](#)
[Installation Manuals - Auteldac 5 Zone 1 Ex Certified Hazardous Area Telephone Installation and User Guide](#)
[Literature - AUTEILDAC 5 - ATEX Approved Hazardous Area Telephone](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
GTC-212-02-5020-410-SPEC-EN | REV 2/2024