



Auteldac 5 (Analogue), steel cord, 0 button; CB, ATEX, noise cancelling

By GAI-Tronics
Catalog # [212-02-5020-B00](#)

The Auteldac 5 (A5) telephone is an ATEX and IECEx approved, weather resistant unit, designed to withstand arduous industrial atmospheres and environmental extremes.



Application

Hazardous Areas

General

| | |
|-----------------------|---|
| CE Compliant | Yes |
| Color | Black |
| Connectivity Options | Analogue |
| Mount location | Surface-Mount |
| Operating Temperature | -20° C up to +60° C |
| Output Level Ringer | 90 dBA @ 2 ft. |
| Signal Type | Analogue |
| Type | <ul style="list-style-type: none">• 0 Button• CB (Central Battery) |
| Weather Resistant | Yes |

Dimensions

| | |
|------------|---------------------------|
| Dimensions | 5.5 in x 7.5 in x 11.5 in |
| Height | 11.5 in |
| Length | 5.5 in |
| Weight | 7 lb |
| Width | 7.5 in |

Electrical Ratings

| | |
|--------|------------|
| Signal | Phone Line |
|--------|------------|

Certifications and Compliance

| | |
|---------------|------|
| CE Compliant | Yes |
| Certification | ATEX |

Product Assets

[Installation Manuals - Guide d'installation et d'utilisation for Auteldac 5 Téléphone pour zone à risques certifiée zone 1 Ex](#)
[Installation Manuals - Auteldac 5 Zone 1 Ex Certified Hazardous Area Telephone Installation and User Guide](#)
[Literature - AUTELDAC 5 - ATEX Approved Hazardous Area Telephone](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
GTC-212-02-5020-B00-SPEC-EN | REV 2/2024