

# Auteldac 6 (A6) VoIP Telephone, Stainless-steel Cord (Standard Length)

By GAI-Tronics  
Catalog # [212-02-6008-510](#)

Auteldac 6 is an ATEX and IECEx Zone 1 & Zone 21 certified VoIP telephone, providing simple network connectivity extending SIP access to hazardous area industrial atmospheres and environmental extremes.



## Features

- IECEx/ATEX Zone 1 VoIP telephone
- II 2 GD Certified for Gas and Dust
- PoE or Local Power
- Session Initiation Protocol (SIP)
- Webpage Browser Configuration
- 18 Button Keypad
- Operating Temperature -40°C/F to +60°C/140°F
- User Adjustable Output Sounder
- User Configurable Relay Output
- Weather Resistant to IP66
- Armoured Stainless Steel Cord
- Headset Connectivity As Standard
- CE Compliant

## General

CE Compliant	Yes
Connectivity Options	VoIP
Humidity	Up to 95% (non-condensing)
Operating Temperature	-40°C (F) to +60°C (+140°F)
Type	18 Full Button Keypad

## Dimensions

Weight 7.7 lb

## Certifications and Compliance

CE Compliant Yes

## Product Assets

- [Certifications - IECEx Certificate of Conformity - Auteldac 6](#)
- [Certifications - Auteldac 6 - A6 - Declaration of Conformity](#)
- [Certifications - EU Type Examination Certificate CML 19ATEX5496 Issue 1](#)
- [Configuration Guide - VoIP Telephone Configuration Guide: Firmware versions 1193 Telephones \(v1.08\); 1201 Telephones for Auteldac 6 \(v1.08\)](#)
- [Installation Manuals - Auteldac 6 Installation and User Guide](#)
- [Literature - Auteldac6 - Zone 1 Hazardous Area VoIP Telephone](#)
- [Video - Learn more about Auteldac 6](#)