



Titan (SMART analogue), yellow, steel cord, 18 button (CE Marked)

By GAI-Tronics
Catalog # [226-02-000J-222](#)

Titan's aluminium body is robust and designed to last longer in hostile outdoor environments. Along with weather and vandal resistance, the Titan range meets the acoustic performance, reliability and varying applications demanded by today's markets. **Self Monitoring and Reporting Telephones** can be integrated with GAI-TRONICS' **TMA monitoring and maintenance software**. **SMART** gives advanced features including remote programming, fault monitoring and call logging, all from a line-powered telephone capable of operating up to 7km from the exchange on a two-wire cable.



General

CE Compliant	Yes
Color	Yellow
Connectivity Options	SMART Analogue
Mount location	Surface-Mount & Post-Mounting
Operating Temperature	-20° C to +60° C
Output Level Ringer	80 dBA @ 2 ft.
Signal Type	Analog
Storage Temperature Range	-40° C to +70° C
Type	18 Button
Weather Rating	IP66

Dimensions

Dimensions	5.1 in x 8.07 in x 14.5 in
Height	14.5 in
Length	5.1 in
Weight	11 lb
Width	8.07 in

Electrical Ratings

Signal	Phone Line
--------	------------

Certifications and Compliance

CE Compliant	Yes
--------------	-----

Product Assets

[Certifications - Titan and Commander SMART Analogue Telephones Declaration of Conformity](#)
[Installation Manuals - Installation and User Guide for Titan Telephone \(1088\) Commander Telephone \(1089\) SMART models](#)
[Literature - Titan - Metal Bodied Weather Resistant Telephone \(Analogue, Smart Analogue, VoIP\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
GTC-226-02-000J-222-SPEC-EN | REV 7/2023