

Tough Phone - Analog/SMART (Keypad)

By GAI-Tronics
Catalog # 226-005

The Tough Phone series was developed for public and industrial areas requiring a virtually indestructible telephone. Housed in a 1/4-inch thick, sand-cast aluminum, weatherproof enclosure and coated with an exterior polyurethane finish. SMART Models include the ability to be centrally monitored for health status via our TMA software.



Features

- Cast Aluminum Enclosure with Polyurethane Finish
- Telephone Line Powered
- No External Power Needed
- Braille Metallic Keypad
- Handset with Noise-canceling Microphone and 15-inch Armored Cord
- Hearing Aid Compatible
- Volume Control Push Button (Front Panel)
- Non-movable Hookswitch
- Surface-mount
- Remote Programming
- Phone's Health Status Reported to Central P.C.
- Programmable Polling or Call-in Scheduling
- Conformal-coated PCBA
- Dual Output Control
- FCC & IC Certified, UL60950 Listed
- TMA Compatible

General

Application	Industrial Areas Public Areas
Color	Gray
Connectivity Options	Analog/SMART
Mount location	Surface-Mount
Output Level Ringer	74 dBA @ 2 ft.
Signal Type	Analog
Type	Keypad
Weather Rating	NEMA 3R

Dimensions

Dimensions	6.1 in x 9.7 in x 13.5 in
Height	13.5 in
Length	6.1 in
Weight	18 lb
Width	9.7 in

Electrical Ratings

Signal	Phone Line
--------	------------

Certifications And Compliance

Certified Listed	UL/IC/FCC
------------------	-----------

Product Assets

- [Brochures - Rugged Telephone Brochure](#)
- [Installation Manuals - Telephone Management Application Installation Bulletin](#)
- [Installation Manuals - SMART Handset Telephones with Keypads \(Model 226-005, 246-005, 256-005, and 276-005\)](#)
- [Installation Manuals - Telephone Management Application \(TMA\) User Guide](#)
- [Literature - Telephone Management Application \(TMA\)](#)
- [Literature - SMART Rugged Telephones - Keypad](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
GTC-226005-SPEC-EN | REV 6/2024