

Indoor Rugged Telephone - Analog/SMART (Auto-dial)

By GAI-Tronics
Catalog # 247-005

This indoor series telephone is constructed of a high-impact, non-metallic enclosure with an industrial strength, six-foot (extended) Hytrel® handset cord. SMART models include the ability to be centrally monitored for health status via our TMA software.



Features

- Telephone Line Powered
- No External Power Needed
- Auto-dial or Ring-down Operation
- Handset with Noise-canceling Microphone and Hytrel® Coiled Cord (6-ft extended)
- Hearing Aid Compatible Handset
- Volume Control Push Button (Front Panel)
- Non-movable Hookswitch
- Remote Programming
- Phone's Health Status Reported to Central P.C.
- Programmable Polling or Call-in Scheduling
- Dual Output Control
- Conformal Coated PCBA
- Three Number Rollover - Unit Dials up to Three Different Numbers to Ensure
- Emergency Calls are Answered
- FCC & IC Certified, UL60950 Listed
- TMA Compatible

General

Application	Indoor Use
Color	Gray
Connectivity Options	Analog/SMART
Mount location	Surface-Mount
Output Level Ringer	90 dBA @ 2 ft.
Signal Type	Analog
Type	Auto-Dial
Weather Rating	Indoor

Dimensions

Dimensions	6.9 in x 8 in x 9.5 in
Height	9.5 in
Length	6.9 in
Weight	4.8 lb
Width	8 in

Electrical Ratings

Signal	Phone Line
--------	------------

Certifications And Compliance

Certified Listed	UL/CSA, FCC, IC
------------------	-----------------

Product Assets

- [Brochures - Rugged Telephone Brochure](#)
- [Installation Manuals - Telephone Management Application Installation Bulletin](#)
- [Installation Manuals - Telephone Management Application \(TMA\) User Guide](#)
- [Installation Manuals - SMART Auto-Dial Handset Telephones Model 227-005, 247-005, 257-005, and 277-005](#)
- [Literature - SMART Rugged Telephones - Auto-dial Literature - Telephone Management Application \(TMA\)](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
GTC-247005-SPEC-EN | REV 6/2024