

Indoor Rugged Telephone - VoIP (Auto-dial)

By GAI-Tronics
Catalog # [247-710](#)

GAI-TRONICS' SIP compatible VoIP Handset Auto-dial Telephones are designed to provide direct point-to-point communication between personnel throughout a facility over an existing Internet Protocol LAN. The telephones are programmed to automatically dial when the handset is taken off-hook (number/address programming via imbedded web browser). The VoIP telephones are intended for connection to a 10/100 BaseT Ethernet SIP network and operate using power-over-Ethernet or an alternative power source.

Features

- Embedded Browser (No Additional Interface required) for Web Page Configuration
- Power Over Ethernet or Alternative 24 - 48 V dc Supply
- SIP Compatible
- RJ45 LAN or WAN Direct Connection
- Four Contact Inputs and Two Relay Outputs
- Real-time Email Fault Reporting
- Anti-corrosive Enclosures
- Surface Mount Models
- Auto-dial Operation
- Hearing Aid Compatible
- Non-moveable Hookswitch
- Noise-cancelling Microphone
- Noise-cancelling Microphone
- Volume Control Pushbutton
- Weather-resistant (Type 3R designs)
- Compatible with TMA (Telephone Management Application) Software

Application

Indoor Use

General

Catalog Number	247-710
Color	Gray
Connectivity Options	VoIP
Mount location	Surface-Mount
Operating Temperature	-4°F to +131°F / -20°C to +55°C
Signal Type	VoIP - SIP
Specifications	UL/CSA, FCC
Storage Temperature Range	-40° C to +70° C



Temperature Rating	-4°F to +131°F (-20°C to +55°C)
Type	Auto-Dial
Weather Rating	Indoor

Dimensions

Cubic Capacity	524.4 cu.in
Depth	6.9 in
Dimensions	6.9 in x 8 in x 9.5 in
Dimensions - Shipping	16.5 x 16.0 x 10.0
Height	9.5 in
Length	6.9 in
Weight	4.8 lb
Width	8 in

Electrical Ratings

Signal	Ethernet
Voltage Rating Description	24-48 VDC or PoE

Certifications And Compliance

Certification	UL/CSA/FCC
Certified Listed	UL/CSA/FCC
Compliance	FCC CRF 47 Part 15

Product Assets

[Brochures - Rugged Telephone Brochure](#)
[Configuration Guide - VoIP Telephone Basic Configuration Guide](#)
[Configuration Guide - VoIP Telephone Configuration Guide:](#)
[Firmware versions 1193 Telephones \(v1.08\); 1201 Telephones for Auteldac 6 \(v1.08\)](#)
[Installation Manuals - VoIP - Software Configuration](#)
[Literature - VoIP Handset Rugged Telephone - Auto-dial](#)
[Specifications - 247710](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
GTC-247710-SPEC-EN | REV 3/2025