

Outdoor Rugged Telephone - VoIP (Keypad)

By GAI-Tronics
Catalog # 256-710



GAI-Tronics' SIP compatible VoIP Handset Surface-mount Telephones are designed to provide direct point-to-point communications between personnel throughout a facility over an existing LAN. The VoIP telephones are intended for connection to a 10/100 BaseT Ethernet SIP network and operate using power-over-Ethernet or an external power source. VoIP telephones are compatible with Cisco's UCM Version 5.0 or newer.

Features

- High-impact, Non-metallic Enclosure
- Embedded Browser (No Additional Interface Required) for Web Page Configuration
- Power Over Ethernet or External 24-48 V dc Supply
- SIP Compatible
- RJ45 LAN or WAN Direct Connection
- Four Contact Inputs and Two Relay Outputs
- Real-time Email Fault Reporting
- Surface-mount
- Full Keypad
- Hearing Aid Compatible
- Conformal-coated PCBA
- Non-moveable Hookswitch
- Handset with Noise-cancelling Microphone and Hytrel® Coiled Cord (6-ft extended)
- Volume Control Pushbutton (Front Panel)
- NEMA 3R Weatherproof Rating
- FCC & IC Certified, UL60950 Listed
- Compatible with TMA (Telephone Management Application) Software

Application

Outdoor & Indoor Use (NEMA 3R)

General

Catalog Number	256-710
Color	Gray
Connectivity Options	VoIP
Mount location	Surface-Mount
Operating Temperature	-4°F to +131°F / -20°C to +55°C
Output Level Ringer	84dBA @ 2 ft.

Signal Type	VoIP - SIP
Specifications	UL/CSA, FCC
Storage Temperature Range	-40° C to +70° C
Temperature Rating	-4°F to +131°F (-20°C to +55°C)
Type	Keypad
Weather Rating	Type 3R

Dimensions

Dimensions	7.4 in x 9.4 in x 13.2 in
Dimensions - Shipping	16.5 x 16.0 x 10.0
Height	13.2 in
Length	7.4 in
Weight	10 lb
Width	9.4 in

Electrical Ratings

Signal	Ethernet
Voltage Rating Description	24-48 VDC or PoE

Certifications And Compliance

Certification	UL/CSA/FCC
Certified Listed	UL/CSA/FCC
Compliance	FCC CRF 47 Part 15

Product Assets

[Brochures - Rugged Telephone Brochure](#)
[Configuration Guide - VoIP Telephone Basic Configuration Guide](#)
[Configuration Guide - VoIP Telephone Configuration Guide: Firmware versions 1193 Telephones \(v1.08\); 1201 Telephones for Auteldac 6 \(v1.08\)](#)
[Literature - VoIP Handset Rugged Telephones](#)
[Specifications - 256710](#)