

# Outdoor Rugged Telephone - Analog/SMART (Auto-dial)

By GAI-Tronics  
Catalog # [257-005](#)

This outdoor series telephone includes a latching door and is constructed of a high-impact, non-metallic enclosure with an industrial strength, six-foot (extended) Hytrel® handset cord. SMART models include the ability to be centrally monitored for health status via our TMA software.

## Features

- High-impact, Non-metallic Enclosure
- Telephone Line Powered
- No External Power Needed
- Auto-dial or Ring-down Operation
- Handset with Noise-canceling Microphone and Hytrel® Coil Cord (6-ft extended)
- Hearing Aid Compatible Handset
- Volume Control Push Button (Front Panel)
- Non-movable Hookswitch
- Surface-mount
- Remote Programming
- Phone's Health Status Reported to Central P.C.
- Programmable Polling or Call-in Scheduling
- Conformal-coated PCBA
- Dual Output Control
- Email Notification of Unit Faults or Reports
- FCC & IC Certified, UL60950 Listed
- TMA Compatible

## Application

Outdoor Use

## General

Catalog Number	257-005
Color	Gray
Connectivity Options	Analog/SMART
Mount location	Surface-Mount
Output Level Ringer	82 dBA @ 2 ft.
Signal Type	Analog



Specifications  
Type  
Weather Rating

UL/IC/FCC  
Auto-Dial  
Type 3R

## Dimensions

Dimensions	7.4 in x 9.4 in x 13.2 in
Dimensions - Shipping	16.5 x 16.0 x 10.0
Height	13.2 in
Length	7.4 in
Weight	10 lb
Width	9.4 in

## Electrical Ratings

Input Voltage	Phone Line
Signal	Phone Line

## Certifications And Compliance

Certified Listed	UL/IC/FCC
------------------	-----------

## Product Assets

[Brochures - Rugged Telephone Brochure](#)  
[Installation Manuals - SMART Auto-Dial Handset Telephones Model 227-005, 247-005, 257-005, and 277-005](#)  
[Installation Manuals - Telephone Management Application](#)  
[Installation Bulletin](#)  
[Installation Manuals - Telephone Management Application \(TMA\)](#)  
[User Guide](#)  
[Literature - Telephone Management Application \(TMA\)](#)  
[Literature - SMART Rugged Telephones - Auto-dial](#)  
[Specifications - 257005](#)