

Flush-panel Telephone - Analog (Auto-dial)

By GAI-Tronics
Catalog # [277-001](#)

The 27x series telephone is designed to flush or surface mount (using 236 series or 238 enclosure). This unit has a brushed stainless steel faceplate with a metallic non-moveable hookswitch. Standard equipment also includes a 29-inch lanyard armored cord and tamper resistant hardware.

Features

- Stainless Steel Construction
- Extended Temperature Range: - 40°F to +140°F
- Auto Dials up to 31 Digits
- Hearing Aid Compatible
- Non-movable Hookswitch
- Volume Control Handset with Noise-cancelling Microphone and 29-inch Armored Cord
- Non-volatile Electronic Memory (Stand-by Batteries Not Required)
- Conformal-coated PCBA
- FCC & IC Certified, UL60950 Listed
- NEMA 3R Weatherproof Rated

Application

Indoor & Outdoor Use

General

Catalog Number	277-001
Color	Silver
Connectivity Options	Analog
Mount location	Flush-Mount
Output Level Ringer	86 dBA @ 2 ft.
Signal Type	Analog



Specifications	UL/IC/FCC
Type	Auto-Dial
Weather Rating	Type 3R

Dimensions

Dimensions	2.44 in x 10.0 in x 12.0 in
Dimensions - Shipping	16.5 x 16.0 x 10.0
Height	12 in
Length	2.44 in
Weight	7 lb
Width	10 in

Electrical Ratings

Input Voltage	Phone Line
Signal	Phone Line

Certifications And Compliance

Certified Listed	UL/IC/FCC
------------------	-----------

Product Assets

[Brochures - Rugged Telephone Brochure](#)
[Installation Manuals - Rugged Analog Auto-Dial Telephones](#)
[Literature - Rugged Telephones - Auto-dial](#)
[Specifications - 277001](#)