



## Flush-panel Handset Telephone - VoIP (Auto-dial)

By GAI-Tronics  
Catalog # [277-710](#)

GAI-Tronics' SIP compatible VoIP Handset Flush-mount Telephones are designed to provide direct point-to-point communications between personnel throughout a facility over an existing LAN. The VoIP telephones are intended for connection to a 10/100 BaseT Ethernet SIP network and operate using power-over-Ethernet or an external power source. VoIP telephones are compatible with Cisco's UCM Version 5.0 or newer.

### Features

- Stainless Steel Construction
- Embedded Browser (No Additional Interface Required) for Web Page Configuration
- Power Over Ethernet or External 24-48 V dc Supply
- SIP Compatible
- RJ45 LAN or WAN Direct Connection
- Four Contact Inputs and Two Relay Outputs
- Flush-Mount
- Autodial
- Conformal-coated PCBA
- Hearing Aid Compatible
- Non-moveable Hookswitch
- Handset with Noise-cancelling Microphone and 29-inch Armored Cord
- Volume Control Pushbutton
- NEMA 3R Weatherproof Rating
- FCC & IC Certified, UL60950 Listed
- Compatible with TMA (Telephone Management Application) Software

### Application

Indoor & Outdoor Use (Type 3R)

### General

Catalog Number	277-710
Color	Silver
Connectivity Options	VoIP
Construction	Front Panel: 14-Gauge Type 304 Brushed Stainless Steel; Dust Cover: 16-Gauge Cold-Rolled Steel With Black Polyurethane Finish
Mount location	Flush-Mount



Operating Temperature	-4°F to +131°F / -20°C to +55 °C
Signal Type	VoIP - SIP
Specifications	UL/CSA, FCC
Storage Temperature Range	-40° C to +70° C
Temperature Rating	-4°F to +131°F (-20°C to +55°C)
Type	Auto-Dial
Weather Rating	Type 3R

### Dimensions

Dimensions	2.44 in x 10.0 in x 12.0 in
Dimensions - Shipping	16.5 x 16.0 x 10.0
Height	12 in
Length	2.44 in
Weight	5.5 lb
Width	10 in

### Electrical Ratings

Signal	Ethernet
Voltage Rating Description	24-48 VDC or PoE

### Certifications And Compliance

Certification	UL/CSA/FCC
Certified Listed	UL/CSA/FCC
Compliance	FCC CRF 47 Part 15

### Product Assets

[Brochures - Rugged Telephone Brochure](#)  
[Configuration Guide - VoIP Telephone Basic Configuration Guide](#)  
[Configuration Guide - VoIP Telephone Configuration Guide:](#)  
[Firmware versions 1193 Telephones \(v1.08\); 1201 Telephones for Auteldac 6 \(v1.08\)](#)  
[Literature - VoIP Handset Rugged Telephone - Auto-dial](#)  
[Specifications - 277710](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved  
GTC-277710-SPEC-EN | REV 3/2025