



## Behavioral Health Flush-Mount VoIP Telephone (Auto-dial)

By GAI-Tronics  
Catalog # [277-712BH](#)

GAI-TRONICS Behavioral Health series of rugged telephones are designed for use in environments where conversation privacy is desired but safety is a concern. The keypad flush-mount handset model is equipped with a shortened, 12-inch handset cord to prevent the handset being used as a weapon. The cord is also short enough to prevent the possibility of strangulation. Its rugged design provides both quality and longevity. The Model 238-003 enclosure can be used if surface mounting is more desirable. Adding an "AC" suffix at the end of either model will increase the handset cord length to 15 inches.



Features

- Stainless Steel Construction
- Embedded Browser (No Additional Interface Required) for Web Page Configuration
- Power Over Ethernet or External 24-48 V dc Supply
- SIP Compatible
- RJ45 LAN or WAN Direct Connection
- Four Contact Inputs and Two Relay Outputs
- Flush-Mount
- Autodial
- Conformal-coated PCBA
- Hearing Aid Compatible
- Non-moveable Hookswitch
- Handset with Noise-cancelling Microphone and 12-inch Armored Cord
- Volume Control Pushbutton
- NEMA 3R Weatherproof Rating
- FCC & IC Certified, UL60950 Listed
- Compatible with TMA (Telephone Management Application) Software

Application

- Rehabilitation Centers
- Correctional Facilities
- Mental Health Facilities

General

Catalog Number	277-712BH
Color	Silver
Connectivity Options	VoIP
Construction	Front Panel: 14-Gauge Type 304 Brushed Stainless Steel; Dust Cover: 16-Gauge Cold-Rolled Steel With Black Polyurethane Finish

Mount location	Flush-Mount
Operating Temperature	-4°F to +131°F / -20°C to +55 °C
Signal Type	VoIP - SIP
Specifications	UL/CSA, FCC
Storage Temperature Range	-40° C to +70° C
Temperature Rating	-4°F to +131°F (-20°C to +55°C)
Type	Auto-Dial
Weather Rating	Type 3R

Dimensions

Dimensions	2.44 in x 10.0 in x 12.0 in
Dimensions - Shipping	13.0 x 12.0 x 8.0
Height	12 in
Length	2.44 in
Weight	5.5 lb
Width	10 in

Electrical Ratings

Signal	Ethernet
Voltage Rating Description	24-48 VDC or PoE

Certifications And Compliance

Certification	UL/CSA/FCC
Certified Listed	UL/CSA/FCC
Compliance	FCC CRF 47 Part 15

Product Assets

[Brochures - Behavioral Health Telephones](#)  
[Configuration Guide - VoIP Telephone Basic Configuration Guide](#)  
[Configuration Guide - VoIP Telephone Configuration Guide: Firmware versions 1193 Telephones \(v1.08\); 1201 Telephones for Auteldac 6 \(v1.08\)](#)  
[Literature - Behavioral Health Flush-mount VoIP Telephones Specifications - 277712BH](#)