

Hazardous Area Analog Telephones - Outdoor - Div. 2

By GAI-Tronics
Catalog # 351-001



Our outdoor model 351-001, provides fully-functional, line-powered communications that are approved for use in Class I, Division 2, Groups A, B, C, D; Class II, Division 2, Groups F and G; Class III classified areas. Our outdoor models have a Type 3R weatherproof rating. Housed in corrosion-resistant enclosures, these units offer superior resistance to chemicals, solvents, salts, and extreme temperatures. Each unit is equipped with a chrome-plated zinc keypad that is fully sealed to prevent entry of dirt, contaminants, and water. The coiled handset cord on our non-metallic model is molded of thermoplastic elastomer to provide outstanding performance, memory, and long life.

Features

- Hazardous Area approved for: Class I, Division 2, Groups A, B, C, D; Class II, Division 2, Groups F and G; Class III
- Economical Communications for Division 2 Areas
- Indoor and Outdoor Models
- Anti-corrosive Enclosures
- Hearing Aid Compatible (HAC) with Pushbutton Volume Control
- Hytrel Coiled Cord or Straight Armored Cord
- Sealed Chrome-plated Keypad
- Extreme Operating Temperature Range
- Conformal Coating on PCBA

General

Color	Blue
Connectivity Options	Analog
Mount location	Surface-Mount
Output Level Ringer	84 @ 1M
Signal Type	Analog
Type	Outdoor Use
Weather Rating	Type 3R

Dimensions

Dimensions	7.4 in x 13.2 in x 9.4 in
Height	9.4 in
Length	7.4 in
Weight	8.2 lb
Width	13.2 in

Electrical Ratings

Signal	Phone Line
--------	------------

Certifications and Compliance

Certification	<ul style="list-style-type: none"> • UL • CSA • IC
Hazardous Rating(s)	<ul style="list-style-type: none"> • Class I, Division 2, Groups A, B, C, D • Class II, Division 2, Groups F & G • Class III, Division 2
Nema Rating	NEMA 3R

Product Assets

[Brochures - Rugged Telephone Brochure](#)
[Installation Manuals - Model 226-002, 341-001, and 351-001](#)
[Div. 2 Industrial Telephones](#)
[Literature - Hazardous Area Telephones](#)

Related Products

- [230-001 - Pole Mounting Kit \(for 25x, 351, 354, XB001\)](#)
- [230-001 - Pole Mounting Kit \(for 25x, 351, 354, XB001\)](#)