

VoIP UL Class I Division 2 Telephone / PagePhone, NEMA 4X

By GAI-Tronics

Catalog # 351-7xxxxx

VoIP Telephone / PagePhone models provide SIP telephone functionality over an existing Ethernet network. When equipped, this telephone can provide a 30W output into a suitable 8 Ohm speaker for multicast broadcasts. Available in four (4) colors (gray, red, orange or yellow).



Features

- UL & cUL approval for: Class I, Division 2, Groups A,B,C,&D T6; Class II, Division 2. Groups F & G; Class III, Division 2
- NEMA 4X Weather Rating
- AC Power, DC Power, or PoE Power Connections
- 6-ft. Hytrel Coiled Cord
- Corrosion-resistant Construction
- Optional 30W Amplifier Output
- Optional Dual Relay Output (programmable)
- Optional Headset Connection

General

Color	Gray, red, orange, or yellow
Connectivity Options	RJ45
Enclosure Type	Engineered Plastic, NEMA 4X

Dimensions

Weight	12.5 lb
--------	---------

Certifications And Compliance

Compliance	NEMA 4X (Enclosure)
Hazardous Rating(s)	Class I, Division 2, Groups A, B, C & D T6
	Class II, Division 2, Groups F & G
	Class III, Division 2

Product Assets

[Installation Manuals - VoIP Page Phones - Wired and WiFi \(Division 2\)](#)

[Installation Manuals - VoIP Telephone - Wired and WiFi \(Division 2\)](#)

[Literature - VoIP UL Class I Division 2 Telephone / PagePhone](#)



A Hubbell brand