

UL Division 1 VoIP Page Phone

By GAI-Tronics
Catalog # 352-712

This unique native VoIP phone comes equipped with an on-board 30W Class D amplifier. Utilized as an IP “telephone” and with a suitable eight ohm (8Ω) loudspeaker connected to the device, the unit enables point to point calling with a “ring” tone generated to the loud-speaker (supplied separately). In multicast operation, the telephone is able to receive group pages. Each device may be a part of up to eight (8) paging groups.



Features

- Built in Class D Amplifier
- Noise-Canceling Microphone
- Volume Adjust

General

Connectivity Options	VoIP
Mount location	Surface-Mount
Type	<ul style="list-style-type: none">• VoIP• Page Phone

Certifications and Compliance

Certification	UL & cUL
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Division 1, Groups B, C, & D• Class II, Division 1, Groups F & G• Class III, Division 1, Part 15 compliant, T6 gas, T4a dust

Product Assets

[Brochures - Rugged Telephone Brochure](#)
[Installation Manuals - VoIP Page Phones - Wired & WiFi \(Model 352-7xx and 352-8xx Division 1\)](#)
[Installation Manuals - VoIP - Software Configuration](#)
[Literature - World's First UL Division 1 VoIP Page Phone](#)