

# NEMA 4X VoIP Rugged Handset Telephone - Model 354-710 Series (Keypad), Gray

By GAI-Tronics  
Catalog # [354-710](#)



GAI-TRONICS' VoIP NEMA 4X Rugged Handset Keypad Telephones are designed to provide direct, point-to-point communications between personnel via an existing Internet Protocol LAN. These telephones are intended for connection to a 10/100 BaseT Ethernet SIP network and operate using Power-over-Ethernet (PoE) or an alternative, external power source. The 354-700 series VoIP Handset Telephone offers standard telephone functionality with active dial tone when the handset is removed from its cradle. This rugged telephone is weatherproof rated as NEMA 4X and will withstand a direct spray wash-down or severe weather conditions. The engineered plastic enclosure, conformal-coated printed circuit board, keypad protective boot, and stainless steel panel and hardware provide the maximum resistance to corrosion.

## General

Application	Outdoor & Indoor Use (NEMA 4X)
Color	Gray
Connectivity Options	VoIP
Mount location	Surface-Mount
Operating Temperature	-4°F to +131°F / -20°C to +55 °C
Signal Type	VoIP - SIP
Storage Temperature Range	-40° C to +70° C
Temperature Rating	-4°F to +131°F (-20°C to +55°C)
Type	Cord Type: 6-ft. Hytrel Cord Keypad
Weather Rating	Type 4X

## Dimensions

Cubic Capacity	1201.725 cu.in
Depth	10.5 in
Dimensions	14.6 in x 10.9 in x 10.5 in
Height	10.5 in
Length	14.6 in
Weight	15 lb
Width	10.9 in

## Electrical Ratings

Signal	Ethernet
Voltage Rating Description	24-48 VDC or PoE

## Certifications And Compliance

Certification	UL/CSA/FCC
Certified Listed	UL/CSA/FCC
Compliance	FCC CRF 47 Part 15
Nema Rating	4X

## Product Assets

- [Brochures - Rugged Telephone Brochure](#)
- [Configuration Guide - VoIP Telephone Basic Configuration Guide](#)
- [Installation Manuals - NEMA 4X VoIP Telephones](#)
- [Literature - NEMA 4X VoIP Handset Telephone \(Keypad\), Model 354-710 Series](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
GTC-354710-SPEC-EN | REV 6/2024