



NEMA 4X VoIP Rugged Handset Telephone, (Autodial), Armored Cord, Orange, Model 354-711ORAC

By GAI-Tronics

Catalog # [354-711ORAC](#)



GAI-TRONICS VoIP NEMA 4X Handset Auto-dial Telephones are designed to provide direct, point-to-point communications between personnel via an existing Internet Protocol LAN. These telephones are intended for connection to a 10/100 BaseT Ethernet SIP network and operate using Power-over-Ethernet (PoE) or an alternative, external power source. The 354-711 series VoIP Auto-dial Telephone offers true auto-dial functionality when the handset is removed from its cradle. This rugged telephone is weatherproof rated as NEMA 4X and will withstand a direct spray wash-down or severe weather conditions. The engineered plastic enclosure, conformal-coated printed circuit board, and stainless steel panel and hardware provide the maximum resistance to corrosion.

Features

- Non-metallic, Corrosion-proof Enclosure
- NEMA 4X Weather Rating
- SIP Compatible
- Power Over Ethernet or Alternative 24/48 V dc Supply
- Brushed Stainless Steel Front Panel with Push-button Volume Control
- Four Programmable Inputs and Two Contact Closure Outputs
- Conformal-coated Printed Circuit Board

Application

Outdoor & Indoor Use (NEMA 4X)

General

| | |
|---------------------------|---|
| Catalog Number | 354-711ORAC |
| Color | Orange |
| Connectivity Options | VoIP |
| Mount location | Surface-Mount |
| Operating Temperature | -4°F to +131°F / -20°C to +55 °C |
| Signal Type | VoIP - SIP |
| Specifications | UL/CSA, FCC |
| Storage Temperature Range | -40° C to +70° C |
| Temperature Rating | -4°F to +131°F (-20°C to +55°C) |
| Type | <ul style="list-style-type: none">• Cord Type: 15-in. Armored Cord• Keypad |
| Weather Rating | Type 4X |

Dimensions

| | |
|-----------------------|-----------------------------|
| Cubic Capacity | 1201.725 cu.in |
| Depth | 10.5 in |
| Dimensions | 14.6 in x 10.9 in x 10.5 in |
| Dimensions - Shipping | 16.75 x 13.25 x 13.00 |
| Height | 10.5 in |
| Length | 14.6 in |
| Weight | 15 lb |
| Width | 10.9 in |

Electrical Ratings

| | |
|----------------------------|------------------|
| Signal | Ethernet |
| Voltage Rating Description | 24-48 VDC or PoE |

Certifications And Compliance

| | |
|------------------|--------------------|
| Certification | UL/CSA/FCC |
| Certified Listed | UL/CSA/FCC |
| Compliance | FCC CRF 47 Part 15 |
| Nema Rating | 4X |

Product Assets

[Configuration Guide - VoIP Telephone Basic Configuration Guide](#)
[Installation Manuals - NEMA 4X VoIP Telephones](#)
[Installation Manuals - Telephone Installation Safety Rules](#)
[Literature - NEMA 4X VoIP Handset Telephone, \(Auto-dial\), 354-711 Series](#)
[Specifications - 354711ORAC](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
GTC-354711ORAC-SPEC-EN | REV 3/2025