

# NEMA 4X VoIP Rugged Handset Telephone, Autodial, Armored Cord, Yellow

By GAI-Tronics  
Catalog # [354-711YLAC](#)



GAI-TRONICS VoIP NEMA 4X Handset Auto-dial Telephones are designed to provide direct, point-to-point communications between personnel via an existing Internet Protocol LAN. These telephones are intended for connection to a 10/100 BaseT Ethernet SIP network and operate using Power-over-Ethernet (PoE) or an alternative, external power source. This VoIP Auto-dial Telephone offers true auto-dial functionality when the handset is removed from its cradle. This rugged telephone is weatherproof rated as NEMA 4X and will withstand a direct spray wash-down or severe weather conditions. The engineered plastic enclosure, conformal-coated printed circuit board, and stainless steel panel and hardware provide the maximum resistance to corrosion.

## Features

- Non-metallic, Corrosion-proof Enclosure
- NEMA 4X Weather Rating
- SIP Compatible
- Power Over Ethernet or Alternative 24/48 V dc Supply
- Brushed Stainless Steel Front Panel with Push-button Volume Control
- Four Programmable Inputs and Two Contact Closure Outputs
- Conformal-coated Printed Circuit Board

## Application

Outdoor & Indoor Use (NEMA 4X)

## General

Catalog Number	354-711YLAC
Color	Yellow
Connectivity Options	VoIP
Mount location	Surface-Mount
Operating Temperature	-4°F to +131°F / -20°C to +55°C
Signal Type	VoIP - SIP
Specifications	UL/CSA, FCC
Storage Temperature Range	-40° C to +70° C
Temperature Rating	-4°F to +131°F (-20°C to +55°C)
Type	<ul style="list-style-type: none"> <li>• Cord Type: 15-in. Armored Cord</li> <li>• Keypad</li> </ul>
Weather Rating	Type 4X

## Dimensions

Cubic Capacity	1201.725 cu.in
Depth	10.5 in
Dimensions	14.6 in x 10.9 in x 10.5 in
Dimensions - Shipping	16.75 x 13.25 x 13.00
Height	10.5 in
Length	14.6 in
Weight	15 lb
Width	10.9 in

## Electrical Ratings

Signal	Ethernet
Voltage Rating Description	24-48 VDC or PoE

## Certifications And Compliance

Certification	UL/CSA/FCC
Certified Listed	UL/CSA/FCC
Compliance	FCC CRF 47 Part 15
Nema Rating	4X

## Product Assets

[Configuration Guide - VoIP Telephone Basic Configuration Guide](#)  
[Installation Manuals - NEMA 4X VoIP Telephones](#)  
[Installation Manuals - Telephone Installation Safety Rules](#)  
[Literature - NEMA 4X VoIP Handset Telephone, \(Auto-dial\), 354-711 Series](#)  
[Specifications - 354711YLAC](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved  
GTC-354711YLAC-SPEC-EN | REV 3/2025