



RED ALERT® Telephones - Model 392-001

By GAI-Tronics
Catalog # 392-001

GAI-TRONICS' Model 392-001 RED ALERT® Handsfree Telephone is designed to provide clear and reliable communications in almost any environment. The Model 392-001 is considered to be Type 3R weatherproof compliant when installed in a GAI-Tronics surface-mount enclosure, free-standing stanchion, wall-mount stanchion or simply recessed into an existing wall.



Features

- Weather-resistant (Type 3R) Flush-Mount Design
- Telephone Line Powered, (No Battery or External Power Required for Telephone Operation)
- CALL Pushbutton for Keypad Use
- Standard or SMART Operation
- Braille, Sealed Chrome-plated Keypad
- Auto Answer (with Silent Monitoring)
- (2) Programmable Auxiliary Outputs for Peripheral Equipment Control
- Operating Range of -20° C to +60° C
- Call Received When Lit LED
- 14-gauge Brushed Stainless Steel Panel
- 16-gauge Cold-Rolled Steel Back Box with Black Polyurethane Finish
- Silkscreened Graphics
- UL/CSA 60950 Compliant
- FCC Part 68 Certified
- ADA Compliant

General

Color	Silver
Connectivity Options	Analog
Mount location	Flush-Mount
Output Level Speaker	87 dB @ 1 M
Signal Type	Analog
Type	Access Telephones
Weather Rating	Type 4X

Dimensions

Dimensions	4.0 in x 8.0 in x 9.5 in
Height	9.5 in
Length	4.0 in
Weight	7.2 lb
Width	8.0 in

Electrical Ratings

Signal	Phone Line
--------	------------

Certifications and Compliance

Certified Listed	UL/CSA, FCC, IC
------------------	-----------------

Product Assets

[Brochures - Red Alert Telephone Brochure](#)
[Installation Manuals - RED ALERT® 300 Series Emergency Telephone Manual](#)
[Literature - RED ALERT Hands-free Telephones](#)
[Literature - Telephone Management Application \(TMA\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
GTC-392-001-SPEC-EN | REV 7/2023