

RED ALERT® WiFi VoIP Hands-free Telephones - Model 393AL-810A

By GAI-Tronics
Catalog # [393AL-810A](#)

These WiFi VoIP Surface-Mount Telephones are designed to provide direct point-to-point communications between personnel over an existing wireless local area network (WLAN), meeting IEEE 802.11 b/g standards. These telephones will operate from an external dc power source which is the only wiring required for operation.



Application

Emergency Telephone Communications (campuses, parking lots, paths)

General

Color	Yellow
Connectivity Options	VoIP
Mount location	Surface-Mount
Operating Temperature	-4°F to +131°F / -20°C to +55 °C
Output Level Speaker	87 dB @ 1 M
Signal Type	VoIP - SIP
Storage Temperature Range	-40° C to +70° C
Temperature Rating	-4°F to +131°F (-20°C to +55°C)
Type	<ul style="list-style-type: none"> • Emergency Telephones • Keypad • HELP Button & CALL Button
Weather Rating	Type 3R

Dimensions

Dimensions	4.0 in x 8.0 in x 9.5 in
Height	9.5 in
Length	4.0 in
Weight	8.5 lb
Width	8.0 in

Electrical Ratings

Signal	Ethernet
Voltage Rating Description	24-48 VDC or PoE

Certifications and Compliance

Certification	UL/CSA/FCC
Certified Listed	UL/CSA/FCC
Compliance	FCC CRF 47 Part 15

Product Assets

- [Brochures - Red Alert Telephone Brochure](#)
- [Configuration Guide - VoIP Telephone Basic Configuration Guide](#)
- [Configuration Guide - VoIP Telephone Configuration Guide: Firmware versions 1193 Telephones \(v1.08\); 1201 Telephones for Auteldac 6 \(v1.08\)](#)
- [Installation Manuals - RED ALERT® Hands-free WiFi VoIP Telephone Manual](#)
- [Literature - WiFi VoIP Hands-free Telephones - Surface-mount](#)