

RED ALERT® VoIP Hands-free Emergency Telephones - Model 394AL-712

By GAI-Tronics
Catalog # 394AL-712



GAI-TRONICS' RED ALERT® Hands-free VoIP Surface-Mount Telephones are designed to provide direct point-to-point communication between personnel throughout a facility over an existing Internet Protocol LAN. The VoIP telephones are intended for connection to a 10/100 BaseT Ethernet and operate using power-over-Ethernet or an alternative power source. The VoIP telephone features real-time alarm reporting that enables system supervisors to monitor the phone's activity and address callers needs or maintenance issues immediately.

Application

Emerg. Telephone Comm., wireless (campuses, parking lots, paths)

General

Color	Yellow
Connectivity Options	VoIP
Mount location	Surface-Mount
Operating Temperature	-4°F to +131°F / -20°C to +55°C
Output Level Speaker	87 dB @ 1 M
Signal Type	VoIP - SIP
Storage Temperature Range	-40° C to +70° C
Temperature Rating	-4°F to +131°F (-20°C to +55°C)
Type	<ul style="list-style-type: none"> Emergency Telephones HELP Button
Weather Rating	Type 3R

Dimensions

Dimensions	4.0 in x 8.0 in x 9.5 in
Height	9.5 in
Length	4.0 in
Weight	7.8 lb
Width	8.0 in

Electrical Ratings

Signal	WiFi
Voltage Rating Description	24-48 VDC

Certifications and Compliance

Certification	UL/CSA/FCC
Certified Listed	UL/CSA/FCC
Compliance	FCC CRF 47 Part 15

Product Assets

[Brochures - Red Alert Telephone Brochure](#)
[Configuration Guide - VoIP Telephone Basic Configuration Guide](#)
[Configuration Guide - VoIP Telephone Configuration Guide: Firmware versions 1193 Telephones \(v1.08\); 1201 Telephones for Auteldac 6 \(v1.08\)](#)
[Installation Manuals - RED ALERT® Hands-free VoIP Telephone Manual](#)
[Literature - VoIP Hands-free Telephones - Surface-mount](#)

Related Products

[Front Panel Replacement/Upgrade Kit for 394AL-702](#)