

LED Strobe, 120 V ac

By GAI-Tronics
Catalog # 540-001

The Model 540-001 LED Strobe features an integral LED tower with constant-on and flashing operations. In addition, the LED strobe provides a secondary contact output for activation of external auxiliary equipment. The Model 540-001 LED Strobe is specifically designed to operate with all GAI-TRONICS' emergency and SMART telephones, providing 240 flashes per minute when the telephone is in use. GAI-TRONICS' emergency telephones are typically installed in many types of public areas such as, college campuses, parking garages, shopping malls, hospitals, sports arenas, amusement parks and more.

Features

- High Visibility, Even in Daylight
- Low Power Consumption (.39 Amperes)
- UL Listed for Outdoor Wet Locations
- Low Operating Temperature
- 240 Flashes Per Minute
- UL/cUL Listed
- Dry Contact Closure Output
- 120 V ac Input

General

UPC 850025795050
Weather Rating UL "Outdoor Wet" Locations

Dimensions

Height 7 in
Width 6.5 in



Certifications and Compliance

Certified Listed UL 1638 / CSA C22.2 No. 205-12

Product Assets

[Installation Manuals - Model 4115A Surface-Mount Strobe Mounting Bracket Assembly](#)
[Installation Manuals - Model 540-001 LED Strobe with Constant-On Feature](#)
[Literature - LED Strobe with 4115A Surface-Mount Strobe Mounting Bracket Assembly](#)
[Sales Drawings - Strobe Mounting Details - 4115A](#)

Related Products

[234SBA - RED ALERT® Tower Broadcast Assembly \(234SBAxx\)](#)
[234 - RED ALERT® Tower - Model 234](#)
[234FS-ER - RED ALERT® Compact Tower \(Model 234FS Series\)](#)
[234SBM - RED ALERT® Tower Broadcast Module \(234SBMxx\)](#)