



Low Voltage LED Strobe, 12-24 V dc

By GAI-Tronics
Catalog # [541-001](#)

The Low Voltage LED Strobe offers constant on/off modes with flashing operation in a low-voltage, 12-24 V dc package. The 541-001 also includes a secondary contact closure output for auxiliary equipment control. In the constant-on mode, the glow of the LED tower remains steady for location purposes and, when activated, will flash at a rate of 240 flashes per minute.

General

Weather Rating UL "Outdoor Wet" Locations

Dimensions

Height 7 in
Width 6.5 in



Certifications and Compliance

Certified Listed UL 1638A / CSA C22.2 No. 205-12

Product Assets

[Installation Manuals - Model 4115A Surface-Mount Strobe Mounting Bracket Assembly](#)
[Installation Manuals - Model 541-001 LED Strobe with Constant-On/Off Modes](#)
[Literature - Low Voltage LED Strobe \(Model 541-001\)](#)
[Sales Drawings - Strobe Mounting Details - 4115A](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
GTC-541-001-SPEC-EN | REV 7/2023