

## Low Voltage LED Strobe, 12-24 V dc

By GAI-Tronics  
Catalog # 541-001

The Low Voltage LED Strobe offers constant on/off modes with flashing operation in a low-voltage, 12-24 V dc package. The 541-001 also includes a secondary contact closure output for auxiliary equipment control. In the constant-on mode, the glow of the LED tower remains steady for location purposes and, when activated, will flash at a rate of 240 flashes per minute.



### General

Weather Rating                      UL "Outdoor Wet" Locations

### Dimensions

Height                                  7 in  
Width                                    6.5 in

### Certifications And Compliance

Certified Listed                      UL 1638A / CSA C22.2 No. 205-12

### Product Assets

- [Installation Manuals - Model 541-001 LED Strobe with Constant-On/Off Modes](#)
- [Installation Manuals - Model 4115A Surface-Mount Strobe Mounting Bracket Assembly](#)
- [Literature - Low Voltage LED Strobe \(Model 541-001\)](#)
- [Sales Drawings - Strobe Mounting Details - 4115A](#)