

Plant Paging Station

By GAI-Tronics
Catalog # [670-002](#)

Hazardous Area Speaker Amplifier Station for 24 VDC operation, FM- and CSA-approved for selected Division 1 areas.



General

Color	Gray
Material	Aluminum
Output Level Speaker	8 / 16 Ohm
Power	12 W
Series	Page/Party®
Signal Type	Analog
Weather Rating	Indoor

Dimensions

Cubic Capacity	579.544 cu.in
Depth	5.6
Height	13.1 in
Weight	27 lb
Width	7.9 in

Electrical Ratings

Signal	33 Ohm
--------	--------

Certifications and Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 1

Product Assets

[Brochures - Page/Party® Solutions Brochure](#)
[Brochures - Page/Party® Accessories Guide](#)
[Installation Manuals - 24 VDC Explosion-proof Speaker Station - Model 670-002](#)
[Installation Manuals - 700 Series 24 VDC Page/Party® System Design and Installation](#)