

## Plant Paging Station

By GAI-Tronics  
Catalog # 670-002

Hazardous Area Speaker Amplifier Station for 24 VDC operation,  
FM- and CSA-approved for selected Division 1 areas.



### General

Color	Gray
Material	Aluminum
Output Level Speaker	8 / 16 Ohm
Power	12 W
Series	Page/Party®
Signal Type	Analog
Weather Rating	Indoor

### Dimensions

Cubic Capacity	579.544 cu.in
Depth	5.6
Height	13.1 in
Weight	27 lb
Width	7.9 in

### Electrical Ratings

Signal	33 Ohm
--------	--------

### Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 1

### Product Assets

- [Brochures - Page/Party® Solutions Brochure](#)
- [Brochures - Page/Party® Accessories Guide](#)
- [Installation Manuals - 700 Series 24 VDC Page/Party® System Design and Installation](#)
- [Installation Manuals - 24 VDC Explosion-proof Speaker Station - Model 670-002](#)