

## Plant Paging/Intercom Amplifier

By GAI-Tronics  
Catalog # [701-307](#)

Handset/Speaker Amplifier, 24 VDC with Magnetic Hookswitch,  
FM Approved



### General

Color	Gray
Material	Steel
Output Level Speaker	8 / 16 Ohm
Power	12 W
Series	Page/Party <sup>®</sup>
Signal Type	Analog
Weather Rating	Indoor

### Dimensions

Cubic Capacity	426.465 cu.in
Depth	6.5
Height	8.1 in
Weight	6.8 lb
Width	8.1 in

### Electrical Ratings

Signal	33 Ohm
--------	--------

### Certifications and Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

### Product Assets

[Brochures - Page/Party<sup>®</sup> Solutions Brochure](#)  
[Brochures - Page/Party<sup>®</sup> Accessories Guide](#)  
[Installation Manuals - Handset/Speaker Amplifier \(24 V DC\) - Model 701-307](#)  
[Kit Manuals - PVC Coil Cord Replacement Kit](#)