

Plant Paging/Intercom Station

By GAI-Tronics
Catalog # 730-104

Outdoor Wall Station, Single-Party Line, NRTL Listed for USA
and Canada Class I, Div. 2, Groups A, B, C, D



General

Color	Gray
Material	Steel / GRP
Output Level Speaker	8 / 16 Ohm
Power	12 W
Series	Page/Party®
Signal Type	Analog
Weather Rating	Outdoor

Dimensions

Cubic Capacity	1670.97 cu.in
Depth	10.5
Height	14.6 in
Weight	16.4 lb
Width	10.9 in

Electrical Ratings

Signal	33 Ohm
--------	--------

Certifications and Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

Product Assets

[Brochures - Page/Party® Solutions Brochure](#)
[Brochures - Page/Party® Accessories Guide](#)
[Installation Manuals - Installation of 700 Series 120 VAC Page/Party® Systems](#)

Related Products

[733-001 - 733-001, Weatherproof Non-Metallic Enclosure](#)
[701-302 - Plant Paging/Intercom Amplifier](#)
[230-001 - Pole Mounting Kit \(for 25x, 351, 354, XB001\)](#)