



## Plant Paging/Intercom Station

By GAI-Tronics  
Catalog # 7305-107

Outdoor Wall Station, Multi-Party Line, FM- and CSA-approved for Class I, Division 2; consists of: Amplifier (Model 701-304) and Enclosure (Model 7335-001)



### General

Color	Gray
Material	Steel / GRP
Output Level Speaker	8 / 16 Ohm
Power	12 W
Series	Page/Party®
Signal Type	Analog
Weather Rating	Outdoor

### Dimensions

Cubic Capacity	1670.97 cu.in
Depth	10.5
Height	14.6 in
Weight	16.4 lb
Width	10.9 in

### Electrical Ratings

Signal	33 Ohm
--------	--------

### Certifications and Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

### Product Assets

[Brochures - Page/Party® Solutions Brochure](#)  
[Brochures - Page/Party® Accessories Guide](#)  
[Installation Manuals - Installation of 700 Series 120 VAC Page/Party® Systems](#)

### Related Products

[701-304 - Plant Paging/Intercom Amplifier](#)  
[7335-001 - 7335-001, Weatherproof Non-Metallic Enclosure, 5 Party Line, NEMA 4X rated](#)  
[230-001 - Pole Mounting Kit \(for 25x, 351, 354, XB001\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
GTC-7305-107-SPEC-EN | REV 7/2023